

Type Description	Type	Frequency	Coil	Shielding	Range of Hole Size	Connector	Part ID	Item N.	Cable ID	Item N.
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	3.9 mm - 4.7 mm (0.156 in. - 0.187 in.)	Triax Fischer	9216153.01	U8602001	9122244	U8800091
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	4.7 mm - 5.5 mm (0.187 in. - 0.218 in.)	Triax Fischer	9216154.01	U8602002	9122244	U8800091
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Triax Fischer	9216156.01	U8602004	9122244	U8800091
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	7.9 mm - 9.5 mm (0.312 in. - 0.375 in.)	Triax Fischer	9216158.01	U8602006	9122244	U8800091
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	7.9 mm - 9.5 mm (0.312 in. - 0.375 in.)	Triax Fischer	9216158.01	U8602006	9122244	U8800091
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	9.5 mm - 11.0 mm (0.375 in. - 0.437 in.)	Triax Fischer	9216160.01	U8602008	9122244	U8800091
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	12.7 mm - 14.3 mm (0.5 in. - 0.562 in.)	Triax Fischer	9216163.01	U8602011	9122244	U8800091
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	4.7 mm - 5.5 mm (0.187 in. - 0.218 in.)	Powerlink™	9222217.00	U8609160	9122083	U8800073
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Powerlink™	9222218.00	U8609161	9122083	U8800073
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	7.9 mm - 9.5 mm (0.312 in. - 0.375 in.)	Powerlink™	9222219.00	U8609162	9122083	U8800073
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	9.5 mm - 11.0 mm (0.375 in. - 0.437 in.)	Powerlink™	9222220.00	U8609163	9122083	U8800073
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	7.1 mm - 7.9 mm (0.281 in. - 0.312 in.)	Powerlink™	9222435.00	U8609176	9122083	U8800073
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	12.7 mm - 14.3 mm (0.5 in. - 0.562 in.)	Powerlink™	9222438.00	U8609179	9122083	U8800073
Manual Bolt Hole	Standard	100 kHz - 500 kHz	Absolute Bridge	Shielded	7.9 mm - 9.5 mm (0.312 in. - 0.375 in.)	Powerlink™	9230823.00	U8626099	9122083	U8800073
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	3.9 mm - 4.7 mm (0.156 in. - 0.187 in.)	Microdot	BPM-10	U8600001	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	3.9 mm - 4.7 mm (0.156 in. - 0.187 in.)	Triax Fischer	BPM-10-TF	U8600002	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	4.7 mm - 5.5 mm (0.187 in. - 0.218 in.)	Microdot	BPM-12	U8600003	9102894	U8800041
Manual Bolt Hole	Standard	1 MHz - 3 MHz	Absolute Bridge	Unshielded	4.7 mm - 5.5 mm (0.187 in. - 0.218 in.)	Microdot	BPM-12-3.5WL-1-3M	U8600780	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	4.7 mm - 5.5 mm (0.187 in. - 0.218 in.)	Triax Fischer	BPM-12-TF	U8600005	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	5.5 mm - 6.5 mm (0.218 in. - 0.250 in.)	Microdot	BPM-14	U8600352	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Microdot	BPM-16	U8600007	9102894	U8800041
Manual Bolt Hole	Standard	1 MHz - 3 MHz	Absolute Bridge	Unshielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Microdot	BPM-16-3.5WL-1-3M	U8600777	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Microdot	BPM-16-4OAL	U8609308	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Triax Fischer	BPM-16-TF	U8600008	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	7.1 mm - 7.9 mm (0.281 in. - 0.312 in.)	Microdot	BPM-18	U8600010	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	7.9 mm - 9.5 mm (0.312 in. - 0.375 in.)	Microdot	BPM-20	U8600011	9102894	U8800041
Manual Bolt Hole	Standard	1 MHz - 3 MHz	Absolute Bridge	Unshielded	7.9 mm - 9.5 mm (0.312 in. - 0.375 in.)	Microdot	BPM-20-3.5WL-1-3M	U8600778	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	7.9 mm - 9.5 mm (0.312 in. - 0.375 in.)	Triax Fischer	BPM-20-TF	U8600014	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	9.5 mm - 11.0 mm (0.375 in. - 0.437 in.)	Microdot	BPM-24	U8600017	9102894	U8800041
Manual Bolt Hole	Standard	1 MHz - 3 MHz	Absolute Bridge	Unshielded	9.5 mm - 11.0 mm (0.375 in. - 0.437 in.)	Microdot	BPM-24-3.5WL-1-3M	U8600781	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	9.5 mm - 11.0 mm (0.375 in. - 0.437 in.)	Triax Fischer	BPM-24-TF	U8600567	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	11.0 mm - 12.7 mm (0.437 in. - 0.500 in.)	Microdot	BPM-28	U8600018	9102894	U8800041

Type Description	Type	Frequency	Coil	Shielding	Range of Hole Size	Connector	Part ID	Item N.	Cable ID	Item N.
Manual Bolt Hole	Standard	1 MHz - 3 MHz	Absolute Bridge	Unshielded	11.0 mm - 12.7 mm (0.437 in. - 0.500 in.)	Microdot	BPM-28-3.5WL-1-3M	U8600868	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	11.0 mm - 12.7 mm (0.437 in. - 0.500 in.)	Triax Fischer	BPM-28-TF	U8600020	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	12.7 mm - 14.3 mm (0.5 in. - 0.562 in.)	Microdot	BPM-32	U8600022	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	12.7 mm - 14.3 mm (0.5 in. - 0.562 in.)	Triax Fischer	BPM-32-TF	U8600023	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	14.3 mm - 15.9 mm (0.562 in. - 0.625 in.)	Microdot	BPM-36	U8600024	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	15.9 mm - 17.4 mm (0.625 in. - 0.687 in.)	Microdot	BPM-40	U8600025	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	15.9 mm - 17.4 mm (0.625 in. - 0.687 in.)	Triax Fischer	BPM-40-TF	U8600458	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	17.4 mm - 19.0 mm (0.687 in. - 0.750 in.)	Microdot	BPM-44	U8600459	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Unshielded	17.4 mm - 19.0 mm (0.687 in. - 0.750 in.)	Triax Fischer	BPM-44-TF	U8600569	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	3.9 mm - 4.7 mm (0.156 in. - 0.187 in.)	Microdot	BPMF-10	U8600039	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	3.9 mm - 4.7 mm (0.156 in. - 0.187 in.)	Triax Fischer	BPMF-10-TF	U8600041	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	4.7 mm - 5.5 mm (0.187 in. - 0.218 in.)	Microdot	BPMF-12	U8600043	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	4.7 mm - 5.5 mm (0.187 in. - 0.218 in.)	Microdot	BPMF-12-1.0OAL-BN	U8600044	9102894	U8800041
Manual Bolt Hole	Standard	200 kHz - 1 MHz	Absolute Bridge	Shielded	4.7 mm - 5.5 mm (0.187 in. - 0.218 in.)	Microdot	BPMF-12-200K-1M	U8600046	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	4.7 mm - 5.5 mm (0.187 in. - 0.218 in.)	Triax Fischer	BPMF-12-TF	U8600218	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	5.5 mm - 6.5 mm (0.218 in. - 0.250 in.)	Microdot	BPMF-14	U8600048	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Microdot	BPMF-16	U8600049	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Microdot	BPMF-16-1.5WL	U8600479	9102894	U8800041
Manual Bolt Hole	Standard	200 kHz - 1 MHz	Absolute Bridge	Shielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Microdot	BPMF-16-200K-1M	U8600629	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Triax Fischer	BPMF-16-TF	U8600050	9122244	U8800091
Manual Bolt Hole	Standard	200 kHz - 1 MHz	Absolute Bridge	Shielded	6.5 mm - 7.1 mm (0.250 in. - 0.281 in.)	Triax Fischer	BPMF-16-TF-200K-1M	U8600967	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	7.9 mm - 9.5 mm (0.312 in. - 0.375 in.)	Microdot	BPMF-20	U8600052	9102894	U8800041
Manual Bolt Hole	Standard	200 kHz - 1 MHz	Absolute Bridge	Shielded	7.9 mm - 9.5 mm (0.312 in. - 0.375 in.)	Microdot	BPMF-20-200K-1M	U8600630	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	9.5 mm - 11.0 mm (0.375 in. - 0.437 in.)	Microdot	BPMF-24	U8600057	9102894	U8800041
Manual Bolt Hole	Standard	200 kHz - 1 MHz	Absolute Bridge	Shielded	9.5 mm - 11.0 mm (0.375 in. - 0.437 in.)	Microdot	BPMF-24-200K-1M	U8600631	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	9.5 mm - 11.0 mm (0.375 in. - 0.437 in.)	Triax Fischer	BPMF-24-TF	U8600058	9122244	U8800091
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	11.0 mm - 12.7 mm (0.437 in. - 0.500 in.)	Microdot	BPMF-28	U8600060	9102894	U8800041
Manual Bolt Hole	Standard	200 kHz - 1 MHz	Absolute Bridge	Shielded	11.0 mm - 12.7 mm (0.437 in. - 0.500 in.)	Microdot	BPMF-28-200K-1M	U8600632	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	12.7 mm - 14.3 mm (0.5 in. - 0.562 in.)	Microdot	BPMF-32	U8600062	9102894	U8800041
Manual Bolt Hole	Standard	200 kHz - 1 MHz	Absolute Bridge	Shielded	12.7 mm - 14.3 mm (0.5 in. - 0.562 in.)	Microdot	BPMF-32-200K-1M	U8600633	9102894	U8800041
Manual Bolt Hole	Standard	50 kHz - 500 kHz	Absolute Bridge	Shielded	14.3 mm - 15.9 mm (0.562 in. - 0.625 in.)	Triax Fischer	BPMF-36-TF	U8600067	9122244	U8800091
Manual Bolt Hole	Standard	1 MHz - 3 MHz	Absolute Bridge	Shielded	15.9 mm - 17.4 mm (0.625 in. - 0.687 in.)	Triax Fischer	BPMF-40-TF-1-3M	U8600856	9122244	U8800091
Manual Bolt Hole	Standard	200 kHz - 1 MHz	Absolute Bridge	Shielded	17.4 mm - 19.0 mm (0.687 in. - 0.750 in.)	Microdot	BPMF-44-200K-1M	U8600636	9102894	U8800041
Manual Bolt Hole	Standard	200 kHz - 1 MHz	Absolute Bridge	Shielded	17.4 mm - 19.0 mm (0.687 in. - 0.750 in.)	Triax Fischer	BPMF-44-TF-200K-1M	U8600968	9122244	U8800091