


# DL2R-11



PARAMETER parameter/paramètre	NOMINAL nennwert/nominal	UPPER (+) ober bereich/supérieure	LOWER (-) unterer bereich/inférieure	UNIT meßeinheit/unité
$f_c^1, f_0^2$	2.0	2.1	1.9	MHz
$BW^1, \Delta f_{rel}^2$	45	50	40	%
F	8	10	6	mm
$W_{a6}$	2.5	3.0	2.0	mm
$W_{b6}$	2.0	2.4	1.6	mm
$F_L$	17.0	20.4	13.6	mm
$D_0$	11.0	11.0	10.9	mm
$T_r$	-20/+60	n/a	n/a	°C
$C_r$	35	40	30	dB
$Z_t$	760	850	670	W
$\varphi_t$	-69	-59	-79	°
$Z_r$	346	396	296	W
$\varphi_r$	78	88	68	°
Waveform duration <sup>1</sup> , Echo width <sup>2</sup> , Echobreite <sup>2</sup> , Largeur de l'écho <sup>2</sup>				
-14dB	1.47	1.60	n/a	µs
-20dB	1.64	1.80	n/a	µs

## DL2R-11

