

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230145.00	U8629506	9122083	U8800073
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230385.00	U8614286	9122083	U8800073
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9231352.00	U8629212	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9231697	U8610437	9122083	U8800073
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9231976	U8629548	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403456	U8610972	9122083	U8800073
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP902-50B	U8620026	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP902-60B	U8620339	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.3 in. (7.62 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Microdot	MMP903-50B-1-3M	U8616353	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP905-40B	U8616358	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP905-50B	U8620039	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP905-60B	U8629993	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF902-40B	U8616417	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF902-50B	U8623026	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF902-60B	U8610849	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF903-40B	U8616418	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF903-60B	U8616419	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF905-50B	U8616422	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF905-60B	U8616423	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.03 in. (0.76 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP10B15-9003-60	U8616225	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.03 in. (0.76 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP10B15-9003-60-200K-1M	U8610997	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP10B15-901-50	U8610910	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP10B15-902-60	U8620463	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.3 in. (7.62 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP10B15-903-50-1-3M	U8616207	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP10B15-903-60	U8629855	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP10B15-905-50-1-3M	U8616208	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP10B15-905-60	U8620462	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP10B15-905-60-1-3M	U8250071	9102894	U8800041
Bent Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP302-50B	U8616287	9102894	U8800041
Bent Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-40B	U8616300	9102894	U8800041
Bent Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-50B	U8620298	9102894	U8800041
Bent Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-60B	U8616310	9102894	U8800041

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Bent Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP455-60B-200K-1M	U8616311	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.03 in. (0.76 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP9003-30B	U8616177	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.03 in. (0.76 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP9003-40B	U8616195	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.03 in. (0.76 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP9003-50B	U8616209	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.03 in. (0.76 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP9003-50B-200K-1M	U8620405	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.03 in. (0.76 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP9003-60B	U8610503	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.1 in. (2.54 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP901-30B-200K-1M	U8616181	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP901-40B	U8620143	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP901-50B	U8620146	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP901-60B	U8610505	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.1 in. (2.54 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP901-60B-1-3M	U8620150	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP902-30B	U8620306	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.2 in. (5.08 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP902-30B-1-3M	U8616182	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.2 in. (5.08 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP902-30B-200K-1M	U8616183	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP902-40B	U8620158	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP902-40B-1-3M	U8620159	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP902-40B-200K-1M	U8629793	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP902-50B	U8620164	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.2 in. (5.08 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP902-50B-1-3M	U8620165	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.2 in. (5.08 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP902-50B-200K-1M	U8629913	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP902-60B	U8620169	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP902-60B-1-3M	U8620373	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP903-30B	U8616184	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP903-40B	U8616202	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP903-50B	U8616213	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.3 in. (7.62 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP903-50B-1-3M	U8620179	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.3 in. (7.62 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP903-50B-200K-1M	U8620407	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.3 in. (7.62 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Microdot	MP903-50B-6M	U8616214	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP903-60B	U8620322	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.4 in. (10.16 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP904-40B	U8616204	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.4 in. (10.16 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP904-50B	U8616216	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.4 in. (10.16 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP904-60B	U8616232	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP905-30B	U8616186	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP905-40B	U8610515	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP905-40B-200K-1M	U8616205	9102894	U8800041

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP905-50B	U8620198	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP905-50B-1-3M	U8610859	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP905-50B-200K-1M	U8610860	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP905-60B	U8620203	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP905-60B-1-3M	U8610519	9102894	U8800041
Bent Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-60B	U8610535	9122244	U8800091
Bent Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-60B-1-6M	U8629989	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.03 in. (0.76 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF9003-50B	U8616217	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.03 in. (0.76 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF9003-50B-200K-1M	U8616218	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.03 in. (0.76 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF9003-60B	U8616236	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF901-40B	U8610710	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF901-50B	U8629665	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF902-30B	U8629800	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF902-40B	U8623079	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF902-40B-1-6M	U8623327	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF902-50B	U8623082	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.2 in. (5.08 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF902-50B-1-6M	U8250106	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.2 in. (5.08 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF902-50B-200K-1M	U8616219	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF902-60B	U8623086	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF902-60B-1-6M	U8623087	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF902-60B-200K-1M	U8616237	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.3 in. (7.62 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF903-50B-1-6M	U8600960	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF903-60B	U8623097	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF903-60B-1-6M	U8623098	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF905-30B	U8616192	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF905-30B-1-6M	U8623346	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF905-40B	U8610713	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF905-50B	U8623107	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF905-50B-1-6M	U8616223	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF905-50B-200K-1M	U8616224	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF905-60B	U8623110	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF905-60B-1-6M	U8623111	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF905-60B-200K-1M	U8623112	9122244	U8800091
Bent Shaft	Absolute Bridge	Straight	4 in. (101.6 mm)	0	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Microdot	MXP-40	U8629055	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Microdot	MXP902-40B	U8623385	9102894	U8800041

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF901-40B	U8623132	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF902-40B	U8623134	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF905-50B	U8629714	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF905-60B	U8629716	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.4 in. (10.16 mm)	50 kHz to 500 kHz	0.094 in. (2.39 mm)	Triax Fischer	MYTF904-50B	U8616444	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.4 in. (10.16 mm)	200 kHz to 1 MHz	0.094 in. (2.39 mm)	Triax Fischer	MYTF904-50B-200K-1M	U8623353	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.094 in. (2.39 mm)	Triax Fischer	MYTF905-50B	U8616445	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.094 in. (2.39 mm)	Triax Fischer	MYTF905-50B-200K-1M	U8623354	9122244	U8800091
Bent Shaft	Absolute Bridge	90°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP10B15-905-60-1-3M	U8250071	9102894	U8800041
Bent Shaft	Absolute Bridge	90°	5 in. (127 mm)	0.3 in. (7.62 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP903-50B-200K-1M	U8620407	9102894	U8800041