

U-LWCD

Long Working Distance Condenser



SPECIFICATIONS

Global item code / Local code for USA	3803000 / 6-U190	
Predecessor product information	None	
Product Category	Condenser	
Optical specification	Contrast Method	BF
	Max. N.A.	0.65
	Working distance	11.6 mm
	Applicable objective powers	5X (Widefield: FN 26.5)
Attached method	Frame	Dovetail
ESD function	N/A	
Weight	380 g	
Country of Origin	Japan	

SYSTEM ENVIRONMENT LIMITATIONS FOR OPERATION


Environment	Indoor use
Temperature T0 [°C]	0 – 40
Humidity RH0 [%]	30 – 90

PACKING LIST

Item	Quantity
Condenser	1

U-LWCD

MAIN DIMENSION



(Unit: mm)

· Specifications and appearances are subject to change without any notice or obligation on the part of the manufacturer.

EVIDENT CORPORATION

AM5428 01

Issued in January, 2023