

BX3M-PSLED

Power Supply for LED Lamp House (required with the BXFM)



SPECIFICATIONS

Global item code / Local code for USA	N5730700 / BX3M-PSLED-1-3
Predecessor product information	None
Product Category	Light Source Unit
Rating	Rating Main unit: input: 5 V / 2.5 A DC AC adapter: input: 100-240 V 50-60 Hz 0.4 A output: 5 V DC 2.5A
Power consumption	5.3W, 17.2VA
Brightness adjustment	Adjustment by the knob Current value of maximum brightness: 700 mA
Ventilation	Natural cooling
The number of controllable LED system	1 system
Connecting	LED lamp housing (with LED cable) AC adapter
ESD function	N/A
Weight	0.36 kg
Country of Origin	Japan

SYSTEM ENVIRONMENT LIMITATIONS FOR OPERATION


Environment	Indoor use
Temperature T0 [°C]	5 – 40
Humidity RH0 [%]	Maximum 80% (up to 31°) (no condensation) Usable humidity declines linearly as temperature rises above 31° 34° (70%) to 37° (60%) to 40° (50%)

BX3M-PSLED

PACKING LIST

Item	Quantity
Power supply	1
AC adapter	1
Cable holder	2
LED cable	1

MAIN DIMENSION



(Unit: mm)

· Specifications and appearances are subject to change without any notice or obligation on the part of the manufacturer.