

INDUSTRIAL

38DL PLUS™ Ultrasonic Thickness Gauge

Advanced Features, Simple Operation



EVIDENT

Advanced Features, Simple Operation, Rugged, and Reliable




The 38DL PLUS™ ultrasonic thickness gauge combines ease of use and accuracy with a durable design. Ideally suited for almost every ultrasonic thickness gauging application, this versatile handheld gauge is compatible with a full line of dual and single element transducers. You can use it in applications ranging from wall thinning measurements of internally corroded pipes with dual element probes to very precise thickness measurements of thin or multilayer materials with single element transducers.

The 38DL PLUS gauge comes standard with powerful measurement features and a range of application-specific software options. Its sealed case is designed for IP67 to withstand the rigors of very wet or dusty environments. The color transfective VGA display provides excellent readability from bright sunlight to complete darkness. It features a simple, ergonomic keypad that you can operate with the left or right hand for easy access to all functions.

Key Features

- › Dual and single element transducer compatibility
- › Wide thickness range: 0.08 mm (0.003 in.) to 635 mm (25 in.) depending on material and transducer selection
- › Corrosion thickness gauging with dual element transducers
- › THRU-COAT™ technology and echo-to-echo measurements on painted and coated surfaces
- › Internal Oxide/Scale software option
- › Standard resolution of 0.01 mm or 0.001 in. for all transducers
- › High Resolution software option of 0.001 mm or 0.0001 in. with single element transducers from 2.25 MHz to 30 MHz
- › Multilayer software option for measurements of up to four layers simultaneously
- › High Penetration software option for attenuating materials such as fiberglass, rubber, and thick castings
- › Thickness, velocity, and time-of-flight measurements
- › Differential mode and reduction rate mode
- › Time-based B-scan mode; 10,000 reviewable readings per scan
- › High Dynamic Gain technology with digital filters
- › V-Path Builder for custom V-path compensation
- › Designed for EN15317



Ultrasonic thickness measurements are accurate, reliable, and repeatable. Instant readings can be achieved from one side of a material, making it unnecessary to cut up or destroy the part.

What Makes This Thickness Gauge Different from Others?

The 38DL PLUS™ thickness gauge is built to meet the challenges of demanding applications and withstand tough conditions in the field and on the production floor. Whether you work in wet or dusty conditions, cold or hot climates, or bright or dark areas, the 38DL PLUS gauge can handle any inspection job. Need an instrument tough enough to tolerate shocks, drops, and rough handling? The 38DL PLUS gauge, with its protective rubber boot and military-rugged design, is your answer.


Built for Tough Environments

- › Compact, weighs only 0.814 kg (1.80 lb)
- › Rugged, designed for IP67
- › Explosive atmosphere: tested using MIL-STD-810F, Method 511.4, Procedure I
- › Shock tested using MIL-STD-810F, Method 516.5, Procedure I, 6 cycles each axis, 15 g, 11 msec half sine
- › Vibration tested using MIL-STD-810F, Method 514.5, Procedure I, Annex C, Figure 6, general exposure: 1 hour each axis
- › Wide operating temperature range
- › Protective rubber boot with gauge stand
- › Color transfective VGA display with indoor and outdoor color settings for excellent clarity




Designed for Easy Operation

- › Simple keypad for right hand/left hand operation
- › Easy operator interface with direct access to all functions
- › Internal and external microSD™ memory card storage
- › USB and RS-232 communication ports
- › Alphanumeric data logger with 475,000 thickness readings or 20,000 waveforms
- › VGA output to connect to computer or monitor
- › Default/Custom dual element transducer setups
- › Default/Custom single element transducer setups
- › Password protected function enables locking of instrument features



Outdoor display setting, A-scan mode



Indoor display setting, B-scan mode



38DL PLUS thickness gauge with standard protective rubber boot

Thickness Measurements on Internally Corroded Metals

One of the major applications of the 38DL PLUS™ gauge is measuring the remaining thickness of pipes, tubes, tanks, pressure vessels, hulls, and other structures affected by corrosion or erosion. Dual element transducers are most commonly used for these applications.

- › Automatic Probe Recognition for standard D79X series dual element transducers
- › Ten custom dual element transducer setups
- › Optimized default gain during calibration for dual element transducer
- › V-Path Builder for custom V-path compensation
- › Calibration doubling warning when echo doubling may occur during calibration
- › THRU-COAT™ technology and echo-to-echo measurements on painted and coated surfaces
- › High-temperature measurements; up to 500 °C (932 °F)
- › Boiler tube and internal oxide measurements (optional) with M2017 or M2091 single element transducers
- › EMAT transducer (E110-SB) for no-couplant measurements of boiler tubes with external oxide/scale buildup






Encoded B-scan Option

This powerful optional feature enables the 38DL PLUS gauge to be connected to a linear encoded scanner to generate encoded B-scans. The instrument will capture and store the distance traveled information along with corresponding thickness readings. The waveform at the minimum thickness location is also captured. The user can select the distance between measurements and select between bidirectional and unidirectional modes. Up to 10,000 thickness readings can be stored in a single B-scan.




THRU-COAT Technology

This feature uses a single back-wall echo to measure true metal thickness. You can display the metal and coating thicknesses, each adjusted for their correct material sound velocities. There is no need to remove paint and coatings from surfaces. THRU-COAT measurements use the D7906-SM, D7906-RM, and D7908 dual element transducers.





Temperature Compensation

Variations in material temperature affect sound velocity and the accuracy of thickness measurements. The temperature compensation feature enables you to manually enter the calibration block's temperature and the current (high) temperature at the measurement points. The The 38DL PLUS™ gauge automatically displays the temperature-corrected thickness.



Oxide/Scale Measurement Option

This feature uses advanced algorithms to measure the thickness of oxide/scale buildups inside boiler tubes. The gauge simultaneously displays the metal thickness of the boiler tube and the thickness of the oxide layer. Knowing the thickness of the oxide/scale helps predict tube life. We recommend using M2017 or M2091 transducers in this application.





V-Path Builder

This patented feature enables you to build a custom V-path compensation curve for almost any dual element transducer. These curves can be saved and recalled along with custom setups for most dual element transducers. You simply calibrate and enter the known thickness with a minimum of 3 and up to 10 calibration points, and the instrument will create the V-path.

Automatic Probe Recognition

All standard dual element transducers (see chart below) feature Automatic Probe Recognition, which automatically recalls a default V-path correction for each specific transducer.



Dual Element Transducers for Corrosion Gauging

All standard dual element transducers feature Automatic Probe Recognition, which automatically recalls a default V-path correction for each specific transducer.

Transducer	Item Number	Freq. (MHz)	Connector	Tip Dia. mm (in.)	Range (Steel)* mm (in.)	Temp. Range** °C (°F)	Cable	Item Number
D790	U8450002	5.0	Straight	11.00 (0.434)	1.00 to 500.00 (0.040 to 20.000)	-20 to 500 (-5 to 932)	Potted	—
D790-SM	U8450009		Straight				LCMD-316-5B [†]	U8800353
D790-RL	U8450007		90°				LCLD-316-5G [†]	U8800330
D790-SL	U8450008		Straight				LCLD-316-5H	U8800331
D791	U8450010	5.0	90°	11.00 (0.434)	1.00 to 500.00 (0.040 to 20.000)	-20 to 500 (-5 to 932)	Potted	—
D791-RM	U8450011	5.0	90°	11.00 (0.434)	1.00 to 500.00 (0.040 to 20.000)	-20 to 400 (-5 to 752)	LCMD-316-5C	U8800354
D7912	Q4530005	10.0	Straight	7.50 (0.295)	0.50 to 25.00 (0.020 to 1.000)	0 to 50 (32 to 122)	Potted	—
D7913	Q4530006		90°					
D794	U8450014	5.0	Straight	7.20 (0.283)	0.75 to 50.00 (0.030 to 2.000)	0 to 50 (32 to 122)	Potted	—
D797	U8450016	2.0	90°	22.90 (0.900)	3.80 to 635.00 (0.150 to 25.000)	-20 to 400 (-5 to 752)	Potted	—
D797-SM	U8450017		Straight				LCMD-316-5D	U8800355
D7226	U8454013	7.5	90°	8.90 (0.350)	0.71 to 100.00 (0.028 to 4.000)	-20 to 150 (-5 to 300)	Potted	—
D798-LF	U8450019							
D798	U8450018	7.5	90°	7.20 (0.283)	0.71 to 100.00 (0.028 to 4.000)	-20 to 150 (-5 to 300)	Potted	—
D798-SM	U8450020		Straight				LCMD-316-5J	U8800357
D799	U8450021	5.0	90°	11.00 (0.434)	1.00 to 500.00 (0.040 to 20.000)	-20 to 150 (-5 to 300)	Potted	—
D7910	U8454038	5.0	90°	12.7 (0.500)	1.00 to 254 (0.040 to 10.000)	0 to 50 (32 to 122)	Potted	—
MTD705 ^{††}	U8620225	5.0	90°	5.10 (0.200)	1.00 to 19.00 (0.040 to 0.750)	0 to 50 (32 to 122)	LCLPD-78-5	U8800332
D7906-SM ^{†††}	U8450005	5.0	Straight	11.00 (0.434)	1.00 to 50.00 (0.040 to 2.000)	0 to 50 (32 to 122)	LCMD-316-5L	U8800358
D7906-RM ^{†††}	U8450025		90°				LCMD-316-5N	U8800647
D7908 ^{††}	U8450006	7.5	90°	7.20 (0.283)	1.00 to 37.00 (0.040 to 1.500)	0 to 50 (32 to 122)	Potted	—

* Thickness range dependent on material, transducer type, surface conditions, and temperature. Full range may require Gain adjustment.

** Maximum temperature with intermittent contact only.

[†] Stainless steel cable available; consult Olympus for details.

^{††} Not certified to EN15317; The MTD705 is issued a TP103 test certificate in accordance with ASTM E1065.

^{†††} Transducers used with THRU-COAT[®] technology.


Single Element Transducers for Corrosion Gauging

For a complete list of single element transducers, please consult your local representative or visit us online at EvidentScientific.com.

Transducer	Item Number	Freq. (MHz)	Connector	Tip Dia. mm (in.)	Range (Steel)* mm (in.)	Temp. Range** °C (°F)	Cable	Item Number
V260-SM	U8411019	15	Straight	2.00 (0.080)	0.50 to 10.00 (0.020 to 0.400)	0 to 50 (32 to 122)	LCM-74-4	U8800348
V260-RM	U8411018		90°				LCM-74-4	U8800348
V260-45	U8411017		45°				LCM-74-4	U8800348
M2017	U8415002	20	90°	6.35 (0.250)	Steel 0.50 to 12.00 (0.020 to 0.500) Oxide 0.25 to 1.25 (0.010 to 0.050)	0 to 50 (32 to 122)	LCM-74-4	U8800348
M2091	U8415018	20	90°	6.35 (0.250)	Steel 0.50 to 12.00 (0.020 to 0.500) Oxide 0.15 to 1.25 (0.006 to 0.050)	0 to 50 (32 to 122)	LCM-74-4	U8800348
E110-SB	U8471001	—	Straight	28.50 (1.250)	2.00 to 125.00 (0.080 to 5.000)	0 to 80 (32 to 176)	LCB-74-4 and 1/2XA/E110	U8800320 U8767104

* Dependent on material, transducer type, surface conditions, and temperature. Full range may require Gain Adjust.

** Maximum temperature with intermittent contact only.



Additional Products

Couplants

Liquid couplant is almost always necessary to provide acoustic coupling between the transducer and the test piece. We offer various types of couplants to suit virtually all applications.

Calibration Test Blocks

Test blocks are necessary for the calibration of ultrasonic thickness gauges and should be used to maintain and verify the accuracy, dependability, and reliability of ultrasonic measurements. Blocks are held to tighter tolerances than stated in the ASTM E797 code. Metric test blocks are available.

Transducer Cables

A wide selection of transducer cables suitable for all ultrasonic thickness gauging instrumentation.

- > Standard
- > Waterproof
- > Heavy duty
 - Teflon
 - Stainless steel

Thickness Measurements on Plastics, Metals, Composites, Glass, Rubber, and Ceramics

When using single element transducers, you can make accurate thickness measurements on metals, plastics, composites, glass, ceramics, and other materials. These transducers are available in a wide range of frequencies, diameters, and connector styles. The High Resolution software option enables you to make very precise measurements at a resolution of 0.0001 in. or 0.001 mm.

- › Standard resolution of 0.01 mm (0.001 in.) for all transducers
- › High Resolution software option can display measurements up to 0.001 mm (0.0001 in.) for single element transducers from 2.25 MHz to 30 MHz
- › High Penetration software option for measurements on attenuating materials such as fiberglass, rubber, and thick castings
- › Multilayer software option for individual thickness measurements of up to four layers simultaneously
- › Thickness, velocity, or time-of-flight measurements
- › Application auto-recall with default and custom setups to simplify thickness measurements

High Penetration Software Option

This option enables you to use low frequency single element transducers (as low as 0.5 MHz) to measure thick or sound attenuating materials such as rubber, fiberglass, castings, and composites.

Multilayer Software Option


This software option calculates and simultaneously displays thickness measurements of up to four individual layers. It also displays the total thickness of selected layers. Typical applications include thickness of barrier layers in plastic fuel tanks, bottle preforms, and soft contact lenses.



Measure the thickness of many materials including plastic, metal, rubber, glass, ceramic, and composites.



Many cast metal parts or sound-attenuating materials can be measured with the High Penetration software option.



The 38DL PLUS thickness gauge can make accurate measurements of up to four individual layers simultaneously.




The High Resolution software option enables thickness measurements of up to 0.001 mm (0.0001 in.) resolution.

Data Logger and PC Interface

The 38DL PLUS™ gauge has a full-featured internal, bidirectional alphanumeric data logger that is designed to easily collect and transfer thickness readings and waveform data.

- Internal memory of 475,000 thickness readings or 20,000 waveforms with thickness readings
- 32-character file name
- 20-character ID# (TML#)
- 9 file formats:
 - Incremental, sequential, sequential with custom point, 2D grid, 2D grid with custom point, 3D grid, 3D custom, boiler, and manual
- Stores up to 4 comments (notes) per ID# (TML)
- Stores comments (notes) at an ID# or to a range of ID#s
- Internal and external microSD memory cards
- File copy with the ability to copy files between internal/external microSD™ memory cards
- Standard USB and RS-232 communication
- Two-way transfer of both single and dual element transducer setups
- Onboard statistical report
- Onboard DB Grid View with three programmable colors
- GageView™ interface program can communicate with the 38DL PLUS instrument using the USB, RS-232 ports, and can read and write to a microSD memory card
- Direct export of internal files to microSD memory card in an Excel compatible CSV (comma-separated values) format



38-Link™ Wireless Communication Adapter

The optional 38-Link wireless adapter enables any existing 38DL PLUS gauge to send and receive data using Bluetooth® or wireless LAN.*

The 38-Link adapter provides three powerful wireless communication capabilities:


- Wireless communication to the Olympus Scientific Cloud (OSC)
- Bluetooth communication to the Link Plus app or other compatible third-party applications
- Bluetooth communication to the optional Link-Wedge software to directly send thickness readings into an active program on your Windows 7 or Windows 10 PC

For more details, see the 38-Link brochure or visit us online at EvidentScientific.com.



GageView™ Program

- The GageView interface program, a Windows-based application, collects, creates, prints, and manages data from the 38DL PLUS gauge
- Create datasets and surveys
- Stored data editing
- View dataset and survey files including thickness readings, gauge setup values, and transducer setup values
- Download and upload thickness surveys to and from the gauges
- Export surveys to spreadsheets and other programs
- Collect snapshot screens
- Print reports such as thickness, setup table, statistics, and color grid
- Upgrade the operating software
- Download and upload single and dual element transducer setup files
- B-scan review



Single Element Transducers for Precision Thickness Measurements

Contact Transducers

Frequency (MHz)	Element Diameter		Transducer	Item Number
	mm	inches		
0.5	25	1.00	M101-SB*	U8400017
1.0	25	1.00	M102-SB*	U8400018
1.0	13	0.50	M103-SB*	U8400020
2.25	13	0.50	M106-RM M106-SM	U8400023 U8400025
2.25	13	0.50	M1036	U8400019
5.0	13	0.50	M109-RM M109-SM	U8400027 U8400028
5.0	6	0.25	M110-RM M110-SM M110H-RM**	U8400030 U8400031 U8400029
10	6	0.25	M112-RM M112-SM M112H-RM**	U8400034 U8400035 U8400033
10	3	0.125	M1016	U8400015
20	3	0.125	M116-RM M116-SM	U8400038 U8400039
20	3	0.125	M116H-RM**	U8400037

* These transducers can only be used with the High Penetration software option.
 ** Use with spring loaded holder.



Sonopen™ Transducers

The Sonopen transducer has a replaceable delay line that is tapered to a small contact area. This transducer makes reliable thickness measurements in applications such as turbine blades and tight radii on plastic containers.



Sonopen – 15 MHz, 3 mm (0.125 IN.) transducer

Straight Handle		Right Angle Handle		45° Handle	
Part	Item Number	Part	Item Number	Part	Item Number
V260-SM	U8411019	V260-RM	U8411018	V260-45	U8411017

Sonopen – Replaceable Delay Lines

Tip Diameter		Part	Item Number
mm	inches		
2.0	0.080	DLP-3	U8770086
1.5	0.060	DLP-302	U8770088
2.0	0.080	DLP-301†	U8770087

† High-temperature delay for use up to 175 °C (350 °F)

Immersion Transducers

Microscan™ immersion transducers are designed to transmit and receive ultrasound in water. Thickness measurements by immersion technique are often preferred when the test piece has a complex geometry or in on-line applications. Typical off-line applications include wall thickness measurements on small-diameter plastic or metal tubing, scanned or rotary measurements, and thickness measurements on sharply curved parts. Transducer focusing may be necessary depending on the application.

RBS-1 Immersion Tank

The RBS-1 immersion tank is designed to simplify ultrasonic thickness measurements using immersion techniques.

Frequency (MHz)	Element Diameter		Transducer	Item Number
	mm	inches		
2.25	13	0.50	M306-SU	U8410027
5.0	13	0.50	M309-SU	U8420001
5.0	6	0.25	M310-SU	U8420004
10	6	0.25	M312-SU	U8420008
15	6	0.25	M313-SU	U8420009
20	3	0.125	M316-SU	U8420011

Delay Line Transducers

Microscan™ delay line transducers provide excellent performance on very thin materials, at elevated temperatures, or with applications that require a high degree of thickness resolution.

Freq. (MHz)	Element Diameter		Transducer	Item Number	Holder	Item Number
	mm	inches				
0.5	25	1.00	M2008*	U8415001	—	
2.25	13	0.50	M207-RB	U8410017	—	
5.0	13	0.50	M206-RB	U8410016	—	
5.0	6	0.25	M201-RM	U8410001	—	
5.0	6	0.25	M201H-RM	U8411030	2127	U8770408
10	6	0.25	M202-RM	U8410003	—	
			M202-SM	U8410004		
10	6	0.25	M202H-RM	U8507023	2127	U8770408
10	3	0.125	M203-RM	U8410006	—	
			M203-SM	U8410007		
20	3	0.125	M208-RM	U8410019	—	
			M208-SM	U8410020		
20	3	0.125	M208H-RM	U8410018	2133	U8770412
20	3	0.125	M2055**	U8415013	—	
30	6	0.25	V213-BC-RM**	U8411022	—	

* These transducers can only be used with the High Penetration software option.

** Delay line is not replaceable on these transducers.




Replaceable Delay Lines

Delay lines function as a protective buffer between the surface of the test piece and the transducer element.

Element Diameter		Delay Line		Maximum Thickness Measurement Limit*					
mm	inches	Part	Item Number	Steel - Mode 2		Steel - Mode 3		Plastic - Mode 2	
				mm	inches	mm	inches	mm	inches
13	0.50	DLH-2	U8770062	25	1.0	13	0.5	13	0.5
6	0.25	DLH-1	U8770054	25	1.0	13	0.5	13	0.5
3	0.125	DLH-3	U8770069	13	0.5	5	0.2	5	0.2

* Exact range depends on material sound velocity, transducer frequency, part geometry, and surface condition.



38DL PLUS™ Specifications*

Measurements

Dual element transducer measurement mode	Time interval from a precision delay after the excitation pulse to the first echo
THRU-COAT™ measurement	Measurement of true metal and coating thicknesses with a single back-wall echo (with D7906-SM and D7908 transducers)
Thru-Paint Echo-to-Echo	Time interval between two successive back-wall echoes to eliminate paint or coating thickness
Single element transducer measurement modes	Mode 1: Time interval between the excitation pulse and the first back-wall echo Mode 2: Time interval between the delay line echo and the first back-wall echo (with delay or immersion transducers) Mode 3: Time interval between successive back-wall echoes following the first interface echo after the excitation pulse (with delay line or immersion transducers) Oxide: optional Multilayer mode: optional
Thickness range	0.080 mm to 635.00 mm (0.003 in. to 25.000 in.) depending on material, transducer surface conditions, temperature, and selected configuration
Material velocity range	0.508 mm/μs to 13.998 mm/μs (0.020 in./μs to 0.551 in./μs)
Resolution (selectable)	Low: 0.1 mm (0.01 in.) Standard: 0.01 mm (0.001 in.) High Resolution (optional): 0.001 mm (0.0001 in.)
Transducer frequency range	Standard: 2.0 MHz to 30 MHz (-3 dB) High Penetration (optional): 0.50 MHz to 30 MHz (-3 dB)

General

Operating temperature range	-10 °C to 50 °C (14 °F to 122 °F)
Keypad	Sealed, color-coded keypad with tactile and audible feedback
Case	Impact-resistant and water-resistant, gasketed case with sealed connectors; designed for IP67
Dimensions (W x H x D)	Overall: 125 mm x 211 mm x 46 mm (4.92 in. x 8.31 in. x 1.82 in.)
Weight	0.814 kg (1.80 lb)
Power supply	AC/DC adapter, 24 V; lithium-ion battery 23.760 Wh; or 4 AA auxiliary batteries
Battery life, lithium-ion	Operating time: minimum 12.6 h, 14 h typical, 14.7 h maximum Fast charge: 2 h to 3 h
Standards	Designed for EN15317
Explosive atmosphere	Tested using MIL-STD-810G, Method 511.5, Procedure I

Display

Color transfective VGA display	Liquid crystal display area: 56.16 mm x 74.88 mm (2.2 in. x 2.95 in.)
Rectification	Full wave, RF, half-wave positive, or half-wave negative

Inputs/Outputs

USB	1.0 client
RS-232	Yes
Memory card	Maximum capacity: 2 GB external microSD™ memory card
Video output	VGA output standard

Internal Data logger

Data logger	The 38DL PLUS instrument identifies, stores, recalls, clears, and transmits thickness readings, waveform images, and gauge configuration information through the standard RS-232 serial port or USB port.
Capacity	475,000 thickness measurements or 20,000 waveforms with thickness measurements
File names, IDs, and comments	32-character file names and 20-character alphanumeric location codes with four comments per location
File structures	Nine standard or custom application-specific file structures
Reports	On-gauge reporting of summary with statistics, Min./Max. with locations, Min. review, file comparison, and alarm report

Standard Package

- 38DL PLUS ultrasonic thickness gauge, AC or battery operation, 50 Hz to 60 Hz
- Kits available with standard dual element transducers*
- Charger/AC adapter (100 VAC, 115 VAC, 230 VAC)
- Internal data logger
- GageView™ interface program
- Test block* and couplant
- USB cable
- Rubber protective boot with gauge stand and neck strap
- User's manual
- **Measurement features:** THRU-COAT, Thru-Paint Echo-to-Echo, EMAT compatibility, Min./Max. mode, two alarm modes, differential mode, B-scan, Application Auto-Recall, temperature compensation, Average/Min. mode

Software Options

- 38DLP-OXIDE (U8147014):** Code-activated Internal Oxide measurement software
- 38DLP-HR (U8147015):** Code-activated High Resolution measurement software
- 38DLP-MM (U8147016):** Code-activated Multilayer measurement software
- 38DLP-HP (U8147017):** Code-activated High Penetration (low frequency) measurement software
- 38DLP-EBSCAN (U8147018):** Encoded B-scan software

Optional Accessories

- 38-LINK-BT-U-EN (Q7790104):** 38-Link™ adapter with Bluetooth dongle
- 38-LINK-WF-NA-EN (Q7790113):** 38-Link adapter with Wireless LAN dongle
- 38DLP/EW (U8778348):** Three-year warranty
- 1/2XA/E110 (U8767104):** Filter adapter for E110-SB EMAT transducer
- 38-9F6 (U8840167):** RS-232 cable
- 38-C-USB-IP67 (U8800998):** USB cable for IP67 sealed operation
- 38DLP/RFS (U8780288):** Foot switch, factory installed
- EPLTC-C-VGA-6 (U8840035):** VGA output cable
- MICROSD-ADP-2GB (U8779307):** 2 GB External microSD memory card
- BSCAN-ENC (U8779522):** Encoded B-scan buggy
- 38DLP-ENC-CBC-10 (U8840168):** 10 ft encoder cable



Evident Scientific, Inc.
48 Woerd Avenue
Waltham, MA 02453, USA
(1) 781-419-3900

EVIDENT CORPORATION is certified to ISO 9001, ISO 14001, and OHSAS 18001.

All specifications are subject to change without notice.

All brands are trademarks or registered trademarks of their respective owners and third party entities.

*In the EMEA region, transducers are not included and must be purchased separately.

*In the EMEA region, the test block is not included and must be purchased separately.

38DL PLUS, THRU-COAT, Sonopen, GageView, 38-Link, and Microscan are trademarks of Evident Corporation or its subsidiaries. Copyright © 2023 by Evident.



E0440039EN