


# DL10R-5



PARAMETER parameter/paramètre	NOMINAL nennwert/nominal	UPPER (+) ober bereich/supérieure	LOWER (-) unterer bereich/inférieure	UNIT meßeinheit/unité
$f_c^1, f_0^2$	10.0	11	9	MHz
$BW^1, \Delta f_{rel}^2$	55	65	45	%
F	3	4	2	mm
$W_{a6}$	1.2	1.5	0.9	mm
$W_{b6}$	0.9	1.2	0.6	mm
$F_L$	5.0	6.0	4.0	mm
$D_0$	5.0	5.0	4.9	mm
$T_r$	-20/+60	n/a	n/a	°C
$C_r$	41	46	36	dB
$Z_t$	90	108	72	W
$\varphi_t$	-80	-70	-90	°
$Z_r$	53	64	42	W
$\varphi_r$	-35	-25	-45	°
Waveform duration <sup>1</sup> , Echo width <sup>2</sup> , Echobreite <sup>2</sup> , Largeur de l'écho <sup>2</sup>				
-14dB	0.2	0.4	n/a	µs
-20dB	0.3	0.5	n/a	µs

