


PF2R-24



PARAMETER parameter/paramètre	NOMINAL nennwert/nominal	UPPER (+) ober bereich/supérieure	LOWER (-) unterer bereich/inférieure	UNIT meßeinheit/unité
f_c^1, f_0^2	2.0	2.2	1.8	MHz
$BW^1, \Delta f_{rel}^2$	45	60	30	%
N	45	50	40	mm
W_6	2.9	3.0	2.8	mm
D	24.0	24.0	23.8	mm
D_{eff}	23.2	23.7	22.7	mm
d	0	0.5	0	°
e	0	0.6	0	mm
g_6	3.7	4.1	3.3	°
Tr	-20/60	n/a	n/a	°C
-14dB: Waveform duration ¹ , Echo width ² , Echobreite ² , Largeur de l'écho ²	2.4	3.6	n/a	us
-20dB: Waveform duration ¹ , Echo width ² , Echobreite ² , Largeur de l'écho ²	3.1	4.7	n/a	us

- 1: ASTM E1065
2: prEN 12668-2
3: EN 1330-4:2000

