


PF4R-10



PARAMETER parameter/paramètre	NOMINAL nennwert/nominal	UPPER (+) ober bereich/supérieure	LOWER (-) unterer bereich/inférieure	UNIT meßeinheit/unité
f_c^1, f_0^2	4.0	4.4	3.6	MHz
$BW^1, \Delta f_{rel}^2$	35	45	25	%
N	15.6	17.2	14.0	mm
W_6	1.2	1.3	1.1	mm
D	10.0	10.0	9.9	mm
D_{eff}	9.7	9.9	9.5	mm
d	0	0.8	0	°
e	0	0.6	0	mm
g_6	4.4	4.8	4.0	°
T_r	-20/60	n/a	n/a	°C
-14dB: Waveform duration ¹ , Echo width ² , Echobreite ² , Largeur de l'écho ²	1.5	2.3	n/a	us
-20dB: Waveform duration ¹ , Echo width ² , Echobreite ² , Largeur de l'écho ²	2.4	3.5	n/a	us

- 1: ASTM E1065
2: prEN 12668-2
3: EN 1330-4:2000

