


PF4R-24



PARAMETER parameter/paramètre	NOMINAL nennwert/nominal	UPPER (+) ober bereich/supérieure	LOWER (-) unterer bereich/inférieure	UNIT meßeinheit/unité
f_c^1, f_0^2	4.0	4.4	3.6	MHz
$BW^1, \Delta f_{rel}^2$	30	40	20	%
N	91	100	82	mm
W_6	2.9	3.0	2.8	mm
D	24.0	24.0	23.8	mm
D_{eff}	23.2	23.7	22.7	mm
d	0	0.5	0	°
e	0	0.6	0	mm
g_6	1.8	2.0	1.6	°
T_r	-20/60	n/a	n/a	°C
-14dB: Waveform duration ¹ , Echo width ² , Echobreite ² , Largeur de l'écho ²	1.0	1.5	n/a	us
-20dB: Waveform duration ¹ , Echo width ² , Echobreite ² , Largeur de l'écho ²	1.6	2.4	n/a	us

- 1: ASTM E1065
2: prEN 12668-2
3: EN 1330-4:2000

