

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9222355.00	U8626054	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230088.00	U8626057	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9230296.00	U8629150	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.1 in. (2.54 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9230485.00	U8629930	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230491.00	U8614288	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230817.00	U8614289	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9231019.00	U8629349	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9231340.00	U8623225	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9231351.00	U8610435	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.2 in. (5.08 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Powerlink™	9231419.00	U8626084	9122083	U8800073
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9231693	U8610436	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9231975	U8629547	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9231986	U8629519	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Powerlink™	9232286	U8629961	9122083	U8800073
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Powerlink™	9403367	U8616326	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	10 in. (254 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.094 in. (2.39 mm)	Powerlink™	9403386	U8616328	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403425	U8629722	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Powerlink™	9403429	U8629919	9122083	U8800073
Angle Shaft	Absolute Bridge	30°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403453	U8610966	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403454	U8610967	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.062 in. (1.57 mm)	Powerlink™	9403459	U8616440	9122083	U8800073
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403476	U8629780	9122083	U8800073
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403477	U8629781	9122083	U8800073
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403478	U8629782	9122083	U8800073
Angle Shaft	Absolute Bridge	30°	7 in. (177.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403479	U8629783	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Powerlink™	9403485	U8629834	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.072 in. (1.83 mm)	Powerlink™	9403490	U8629866	9122083	U8800073
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Powerlink™	9403491	U8629867	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Powerlink™	9403492	U8629868	9122083	U8800073
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403505	U8614255	9122083	U8800073
Angle Shaft	Absolute Bridge	30°	10 in. (254 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-100	U8616329	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	12 in. (304.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-120	U8616330	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-30	U8620003	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-40	U8620004	9102894	U8800041

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Microdot	MMP305-40-1-3M	U8629815	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.072 in. (1.83 mm)	Microdot	MMP305-40-1-6M	U8616441	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Microdot	MMP305-40-200K-1M	U8620434	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-50	U8620008	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Microdot	MMP305-50-200K-1M	U8620436	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-60	U8620009	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Microdot	MMP305-60-1-3M	U8620392	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Microdot	MMP305-60-200K-1M	U8620437	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	7 in. (177.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-70	U8616332	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	8 in. (203.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-80	U8616333	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	8 in. (203.2 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Microdot	MMP305-80-200K-1M	U8629892	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	9 in. (228.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-90	U8616334	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	8 in. (203.2 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP452-80	U8616335	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.3 in. (7.62 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Microdot	MMP453-40-1-3M	U8620279	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP455-30	U8620378	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP455-40	U8620280	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.072 in. (1.83 mm)	Microdot	MMP455-40-6M	U8620443	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP455-50	U8620344	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Microdot	MMP455-50-1-3M	U8620345	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP455-60	U8610969	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Microdot	MMP455-60-1-3M	U8616338	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	7 in. (177.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP455-70	U8616340	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	8 in. (203.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP455-80	U8616341	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	10 in. (254 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF305-100	U8616428	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	10 in. (254 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF305-100-1-6M	U8623349	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF305-30	U8616429	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF305-40	U8623013	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF305-50	U8623016	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF305-60	U8623017	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF451-40	U8610699	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF453-60	U8610489	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF455-40	U8623020	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF455-40-1-6M	U8616426	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF455-40-200K-1M	U8616427	9122244	U8800091

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF455-50	U8623340	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF455-60	U8610624	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF455-60-1-6M	U8629983	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP302-60	U8616291	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	10 in. (254 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP305-100	U8620057	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	12 in. (304.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP305-120	U8616294	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP305-30	U8620058	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP305-40	U8620059	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP305-40-1-3M	U8629811	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP305-40-200K-1M	U8629812	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP305-50	U8620061	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP305-50-1-3M	U8616288	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP305-50-200K-1M	U8620312	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP305-60	U8620062	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP305-60-1-3M	U8610715	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	9 in. (228.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP305-90	U8620355	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	10 in. (254 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP4510-100	U8616320	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.1 in. (2.54 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP4510-40	U8616298	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.2 in. (5.08 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP452-50-1-3M	U8616304	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	12 in. (304.8 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP453-120	U8616322	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	3 in. (76.2 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP453-30	U8610629	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP453-40	U8620078	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.3 in. (7.62 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP453-40-1-3M	U8620079	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.3 in. (7.62 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP453-40-200K-1M	U8616299	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP453-50	U8620080	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.3 in. (7.62 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP453-50-200K-1M	U8629763	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP453-60	U8620081	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP453-60-1-3M	U8623373	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP453-60-200K-1M	U8629678	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Microdot	MP453-60-6M	U8629600	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	7 in. (177.8 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP453-70	U8620255	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	8 in. (203.2 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP453-80	U8616315	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	8 in. (203.2 mm)	0.3 in. (7.62 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP453-80-200K-1M	U8616316	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	9 in. (228.6 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP453-90	U8250103	9102894	U8800041

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.4 in. (10.16 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP454-60	U8616308	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	10 in. (254 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-100	U8620082	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	10 in. (254 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP455-100-1-3M	U8629784	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	11 in. (279.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-110	U8616321	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	12 in. (304.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-120	U8616323	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	12 in. (304.8 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP455-120-1-3M	U8616324	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-30	U8620085	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP455-30-1-3M	U8616295	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP455-30-200K-1M	U8616296	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-40	U8620086	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP455-40-1-3M	U8620087	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP455-40-200K-1M	U8620423	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Microdot	MP455-40-6M	U8620416	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-50	U8620094	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP455-50-1-3M	U8620346	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP455-50-200K-1M	U8629762	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Microdot	MP455-50-6M	U8616306	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-60	U8620097	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP455-60-1-3M	U8620098	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP455-60-200K-1M	U8616309	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	7 in. (177.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-70	U8620440	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	7 in. (177.8 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP455-70-200K-1M	U8620369	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	8 in. (203.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-80	U8616317	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	8 in. (203.2 mm)	0.5 in. (12.7 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP455-80-1-3M	U8620101	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	8 in. (203.2 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP455-80-200K-1M	U8629893	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	9 in. (228.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP455-90	U8616318	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF302-60	u8623362	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.2 in. (5.08 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF302-60-1-6M	u8623363	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF303-60	U8610946	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF303-60-200K-1M	U8610948	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	10 in. (254 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-100	U8616293	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-30	U8623251	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-40	U8610529	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-50	U8623037	9122244	U8800091

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-50-1-6M	U8616289	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-50-200K-1M	U8616290	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-60	U8623338	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-60-1-6M	U8610716	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-60-200K-1M	U8623339	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	7 in. (177.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF305-70	U8623328	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.2 in. (5.08 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF452-40	U8616303	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	3 in. (76.2 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF453-30	U8610530	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	3 in. (76.2 mm)	0.3 in. (7.62 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF453-30-200K-1M	U8623375	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF453-40	U8623045	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF453-50	U8623046	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF453-60	U8610532	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF453-60-1-6M	U8610780	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.3 in. (7.62 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF453-60-200K-1M	U8623374	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	7 in. (177.8 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF453-70	U8629336	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	8 in. (203.2 mm)	0.3 in. (7.62 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF453-80	U8623047	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	10 in. (254 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-100	U8623048	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	11 in. (279.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-110	U8250093	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	12 in. (304.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-120	U8623049	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	3 in. (76.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-30	U8620274	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-40	U8623050	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-40-1-6M	U8623051	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-40-200K-1M	U8610534	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-50	U8623052	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-50-1-6M	U8614273	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	5 in. (127 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-50-200K-1M	U8616307	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-60	U8623053	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-60-1-6M	U8623054	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-60-200K-1M	U8623055	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	7 in. (177.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-70	U8623056	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	8 in. (203.2 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-80	U8623057	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.4 in. (10.16 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF304-40	U8616432	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF305-40	U8623128	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	1 MHz to 6 MHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF305-40-1-6M	U8623129	9122244	U8800091

Type	Coil	Tip Angle	Length	Drop	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Angle Shaft	Absolute Bridge	30°	4 in. (101.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF305-40-F-16	U8623130	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	9 in. (228.6 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF455-90	U8616434	9122244	U8800091
Angle Shaft	Absolute Bridge	45°	7 in. (177.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.094 in. (2.39 mm)	Microdot	MYP455-70	U8616435	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.062 in. (1.57 mm)	Microdot	MZP305-60	U8610945	9102894	U8800041
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	200 kHz to 1 MHz	0.062 in. (1.57 mm)	Triax Fischer	MZTF305-50-200K-1M	U8616141	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	6 in. (152.4 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.062 in. (1.57 mm)	Triax Fischer	MZTF305-60	U8623370	9122244	U8800091
Angle Shaft	Absolute Bridge	30°	5 in. (127 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP305-50	U8620008	9102894	U8800041
Angle Shaft	Absolute Bridge	45°	7 in. (177.8 mm)	0.5 in. (12.7 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF455-70	U8623056	9122244	U8800091