

Type	Coil	Frequency	Inner Diameter	Outer Diameter	Connector	Part ID	U8 Number	Cable ID	Item N.
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	12.7 mm (0.5 in.)	27.6 mm (1.09 in.)	Microdot	RR0110-1	U8634001	9102894	U8800041
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	12.7 mm (0.5 in.)	27.6 mm (1.09 in.)	Triax Fischer	RR0110-1-TF	U8634002	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	12.7 mm (0.5 in.)	25.4 mm (1.0 in.)	Triax Fischer	RR0110-5-TF	U8636011	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	13.4 mm (0.53 in.)	27.9 mm (1.10 in.)	Triax Fischer	RR0111-1-TF	U8636012	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	15.24 mm (0.6 in.)	31.75 mm (1.25 in.)	Microdot	RR0112-2	U8636016	9102894	U8800041
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	15.24 mm (0.6 in.)	31.75 mm (1.25 in.)	Triax Fischer	RR0112-2-TF	U8620341	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	15.24 mm (0.6 in.)	29.46 mm (1.16 in.)	Triax Fischer	RR0112-5-TF	U8636018	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	13.72 mm (0.54 in.)	27.9 mm (1.10 in.)	Triax Fischer	RR0112-6-TF	U8636092	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	17.77 mm (0.70 in.)	33.01 mm (1.30 in.)	Triax Fischer	RR0113-5-TF	U8636019	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	20.0 mm (0.788 in.)	35.55 mm (1.4 in.)	Triax Fischer	RR0114-3-TF	U8636021	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	20.32 mm (0.8 in.)	35.55 mm (1.4 in.)	Triax Fischer	RR0114-5-TF	U8636022	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	80 Hz - 4 kHz	20.32 mm (0.8 in.)	38.10 mm (1.5 in.)	Triax Fischer	RR0115-1-TF	U8636117	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	21.84 mm (0.86 in.)	31.75 mm (1.25 in.)	Triax Fischer	RR0115-4-TF	U8636023	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	80 Hz - 4 kHz	8.89 mm (0.35 in.)	19.05 mm (0.75 in.)	Microdot	RR017-1	U8636025	9102894	U8800041
Ring Donut Probes	Reflection Absolute	80 Hz - 4 kHz	8.89 mm (0.35 in.)	19.05 mm (0.75 in.)	Triax Fischer	RR017-5-TF	U8636118	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	50 Hz - 3 kHz	10.16 mm (0.4 in.)	20.32 mm (0.8 in.)	Triax Fischer	RR018-5-TF	U8636027	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	80 Hz - 4 kHz	10.80 mm (0.425 in.)	22.86 mm (0.9 in.)	Triax Fischer	RR019-1-TF	U8636103	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	80 Hz - 4 kHz	12.7 mm (0.5 in.)	25.4 mm (1.0 in.)	Triax Fischer	RR019-2-TF	U8636029	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	80 Hz - 4 kHz	13.21 mm (0.52 in.)	22.86 mm (0.9 in.)	Triax Fischer	RR019-3-TF	U8636030	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	80 Hz - 4 kHz	11.43 mm (0.45 in.)	22.86 mm (0.9 in.)	Triax Fischer	RR019-5-TF	U8636031	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	100 Hz - 5 kHz	13.87 mm (0.546 in.)	26.67 mm (1.05 in.)	Microdot	RR0210-1	U8636109	9102894	U8800041
Ring Donut Probes	Reflection Absolute	100 Hz - 5 kHz	6.35 mm (0.25 in.)	15.24 mm (0.6 in.)	Microdot	RR026-1	U8629109	9102894	U8800041
Ring Donut Probes	Reflection Absolute	100 Hz - 5 kHz	6.35 mm (0.25 in.)	15.24 mm (0.6 in.)	Triax Fischer	RR026-1-TF	U8636032	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	100 Hz - 5 kHz	7.92 mm (0.312 in.)	20.07 mm (0.79 in.)	Triax Fischer	RR028-1-TF	U8636043	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	200 Hz - 10 kHz	12.7 mm (0.5 in.)	25.4 mm (1.0 in.)	Triax Fischer	RR0510-5-TF	U8620470	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	200 Hz - 10 kHz	5.07 mm (0.2 in.)	15.36 mm (0.605 in.)	Triax Fischer	RR056-1-TF	U8620266	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	200 Hz - 10 kHz	13.9 mm (0.55 in.)	27.9 mm (1.10 in.)	Triax Fischer	RR0511-5-TF	U8636123	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	300 Hz - 10 kHz	10.80 mm (0.425 in.)	19.05 mm (0.75 in.)	Triax Fischer	RR057-2-TF	U8636120	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	200 Hz - 10 kHz	10.16 mm (0.4 in.)	19.05 mm (0.75 in.)	Triax Fischer	RR057-5-TF	U8636038	9122244	U8800538

\*All specifications are subject to change without notice.  
 All brands are trademarks or registered trademarks of their respective owners and third party entities.  
 Copyright © 2024 by Evident. REV. 2

# Ring / Donut Probes

## Reflection Absolute

Type	Coil	Frequency	Inner Diameter	Outer Diameter	Connector	Part ID	U8 Number	Cable ID	Item N.
Ring Donut Probes	Reflection Absolute	200 Hz - 10 kHz	8.38 mm (0.33 in.)	17.78 mm (0.7 in.)	Triax Fischer	RR057-6-TF	U8636113	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	200 Hz - 10 kHz	7.62 mm (0.3 in.)	20.70 mm (0.815 in.)	Microdot	RR058-1	U8636039	9102894	U8800041
Ring Donut Probes	Reflection Absolute	200 Hz - 10 kHz	7.62 mm (0.3 in.)	20.70 mm (0.815 in.)	Triax Fischer	RR058-1-TF	U8636040	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	5 kHz - 80 kHz	7.62 mm (0.3 in.)	15.24 mm (0.6 in.)	Microdot	RR1006-5	U8636088	9102894	U8800041
Ring Donut Probes	Reflection Absolute	5 kHz - 80 kHz	7.62 mm (0.3 in.)	15.24 mm (0.6 in.)	Triax Fischer	RR1006-5-TF	U8636102	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	5 kHz - 80 kHz	11.43 mm (0.45 in.)	22.86 mm (0.9 in.)	Triax Fischer	RR1009-5-TF	U8634146	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	500 Hz - 20 kHz	6.35 mm (0.25 in.)	15.24 mm (0.6 in.)	Triax Fischer	RR206-5-TF	U8636041	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	500 Hz - 20 kHz	8.51 mm (0.335 in.)	15.24 mm (0.6 in.)	Triax Fischer	RR207-1-TF	U8636042	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	500 Hz - 20 kHz	9.52 mm (0.375 in.)	18.03 mm (0.71 in.)	Triax Fischer	RR207-2-TF	U8623372	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	500 Hz - 20 kHz	8.89 mm (0.35 in.)	17.78 mm (0.7 in.)	Triax Fischer	RR207-5-TF	U8636116	SPO-6687	U8800538
Ring Donut Probes	Reflection Absolute	500 Hz - 20 kHz	8.50 mm (0.325 in.)	15.11 mm (0.595 in.)	Microdot	RR2007-1	U8636100	9102894	U8800041
Ring Donut Probes	Reflection Absolute	500 Hz - 20 kHz	8.50 mm (0.325 in.)	15.11 mm (0.595 in.)	Triax Fischer	RR2007-1-TF	U8636101	SPO-6687	U8800538