

Type	Coil	Length	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 100 kHz	0.125 in. (3.17 mm)	Triax Fischer	9216190.00	U8623177	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9216191.00	U8623178	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 100 kHz	0.125 in. (3.17 mm)	Powerlink™	9222165.01	U8616094	9122083	U8800073
Straight	Absolute Bridge	4 in. (101.6 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9222202.00	U8616095	9122083	U8800073
Straight	Absolute Bridge	8 in. (203.2 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230093.00	U8614283	9122083	U8800073
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230150.00	U8629146	9122083	U8800073
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230238.00	U8614284	9122083	U8800073
Straight	Absolute Bridge	3 in. (76.2 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230248.00	U8626061	9122083	U8800073
Straight	Absolute Bridge	6 in. (152.4 mm)	100 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230289.00	U8626062	9122083	U8800073
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9230387.00	U8610985	9122083	U8800073
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9231747	U8629260	9122244	U8800091
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	9232093	U8616127	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403359.00	U8629526	9122083	U8800073
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403370	U8614295	9122083	U8800073
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Powerlink™	9403371	U8616327	9122083	U8800073
Straight	Absolute Bridge	3 in. (76.2 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Powerlink™	9403400	U8626127	9122083	U8800073
Straight	Absolute Bridge	4 in. (101.6 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Powerlink™	9403403	U8629527	9122083	U8800073
Straight	Absolute Bridge	4 in. (101.6 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Powerlink™	9403404	U8629528	9122083	U8800073
Straight	Absolute Bridge	6 in. (152.4 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403431	U8629920	9122083	U8800073
Straight	Absolute Bridge	4 in. (101.6 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Powerlink™	9403438	U8629653	9122083	U8800073
Straight	Absolute Bridge	5 in. (127 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Powerlink™	9403448	U8610925	9122083	U8800073
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.062 in. (1.57 mm)	Powerlink™	9403457	U8629765	9122083	U8800073
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.062 in. (1.57 mm)	Powerlink™	9403460	U8616150	9122083	U8800073
Straight	Absolute Bridge	12 in.(304.8 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Powerlink™	9403466	U8629736	9122083	U8800073
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Powerlink™	9403495	U8616151	9122083	U8800073
Straight	Absolute Bridge	10 in. (254 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP-100	U8616168	9102894	U8800041
Straight	Absolute Bridge	12 in.(304.8 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP-120	U8616172	9102894	U8800041
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP-30	U8620002	9102894	U8800041
Straight	Absolute Bridge	3 in. (76.2 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Microdot	MMP-30-1-3M	U8616365	9102894	U8800041
Straight	Absolute Bridge	3 in. (76.2 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Microdot	MMP-30-200K-1M	U8616366	9102894	U8800041
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP-40	U8620010	9102894	U8800041
Straight	Absolute Bridge	4 in. (101.6 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Microdot	MMP-40-1-3M	U8616152	9102894	U8800041
Straight	Absolute Bridge	4 in. (101.6 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Microdot	MMP-40-200K-1M	U8620458	9102894	U8800041
Straight	Absolute Bridge	5 in. (127 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP-50	U8620014	9102894	U8800041
Straight	Absolute Bridge	5 in. (127 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Microdot	MMP-50-200K-1M	U8620460	9102894	U8800041

Type	Coil	Length	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Straight	Absolute Bridge	6 in. (152.4 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP-60	U8620302	9102894	U8800041
Straight	Absolute Bridge	6 in. (152.4 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Microdot	MMP-60-1-3M	U8620016	9102894	U8800041
Straight	Absolute Bridge	6 in. (152.4 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Microdot	MMP-60-200K-1M	U8620461	9102894	U8800041
Straight	Absolute Bridge	8 in. (203.2 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Microdot	MMP-80	U8616165	9102894	U8800041
Straight	Absolute Bridge	10 in. (254 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-100-200K-1M	U8610486	9122244	U8800091
Straight	Absolute Bridge	12 in.(304.8 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-120	U8616173	9122244	U8800091
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-30	U8623012	9122244	U8800091
Straight	Absolute Bridge	3 in. (76.2 mm)	1 MHz to 3 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-30-1-3M	U8616413	9122244	U8800091
Straight	Absolute Bridge	3 in. (76.2 mm)	1 MHz to 6 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-30-1-6M	U8616414	9122244	U8800091
Straight	Absolute Bridge	3 in. (76.2 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-30-200K-1M	U8610885	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-40	U8623019	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	1 MHz to 6 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-40-1-6M	U8629764	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-40-200K-1M	U8623239	9122244	U8800091
Straight	Absolute Bridge	5 in. (127 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-50	U8623022	9122244	U8800091
Straight	Absolute Bridge	5 in. (127 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-50-200K-1M	U8610881	9122244	U8800091
Straight	Absolute Bridge	6 in. (152.4 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-60	U8623023	9122244	U8800091
Straight	Absolute Bridge	6 in. (152.4 mm)	200 kHz to 1 MHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-60-200K-1M	U8610882	9122244	U8800091
Straight	Absolute Bridge	7 in. (177.8 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-70	U8616163	9122244	U8800091
Straight	Absolute Bridge	8 in. (203.2 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-80	U8610878	9122244	U8800091
Straight	Absolute Bridge	9 in. (228.6 mm)	50 kHz to 500 kHz	0.072 in. (1.83 mm)	Triax Fischer	MMTF-90	U8610879	9122244	U8800091
Straight	Absolute Bridge	10 in. (254 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-100	U8620048	9102894	U8800041
Straight	Absolute Bridge	11 in. (279.4 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-110	U8616170	9102894	U8800041
Straight	Absolute Bridge	12 in.(304.8 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-120	U8616175	9102894	U8800041
Straight	Absolute Bridge	12 in.(304.8 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP-120-1-3M	U8616176	9102894	U8800041
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-30	U8620053	9102894	U8800041
Straight	Absolute Bridge	3 in. (76.2 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP-30-1-3M	U8620055	9102894	U8800041
Straight	Absolute Bridge	3 in. (76.2 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP-30-200K-1M	U8620056	9102894	U8800041
Straight	Absolute Bridge	3 in. (76.2 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Microdot	MP-30-6M	U8620064	9102894	U8800041
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-40	U8620067	9102894	U8800041
Straight	Absolute Bridge	4 in. (101.6 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP-40-1-3M	U8620068	9102894	U8800041
Straight	Absolute Bridge	4 in. (101.6 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP-40-200K-1M	U8620069	9102894	U8800041
Straight	Absolute Bridge	5 in. (127 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-50	U8620108	9102894	U8800041
Straight	Absolute Bridge	5 in. (127 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP-50-1-3M	U8620110	9102894	U8800041
Straight	Absolute Bridge	5 in. (127 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP-50-200K-1M	U8620403	9102894	U8800041
Straight	Absolute Bridge	6 in. (152.4 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-60	U8620112	9102894	U8800041

Type	Coil	Length	Frequency	Shaft Size	Connector	Part ID	Item N.	Cable ID	Item N.
Straight	Absolute Bridge	6 in. (152.4 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP-60-1-3M	U8620113	9102894	U8800041
Straight	Absolute Bridge	6 in. (152.4 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP-60-200K-1M	U8610632	9102894	U8800041
Straight	Absolute Bridge	7 in. (177.8 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-70	U8610676	9102894	U8800041
Straight	Absolute Bridge	7 in. (177.8 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Microdot	MP-70-200K-1M	U8616164	9102894	U8800041
Straight	Absolute Bridge	8 in. (203.2 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-80	U8616166	9102894	U8800041
Straight	Absolute Bridge	8 in. (203.2 mm)	1 MHz to 3 MHz	0.125 in. (3.17 mm)	Microdot	MP-80-1-3M	U8620117	9102894	U8800041
Straight	Absolute Bridge	9 in. (228.6 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Microdot	MP-90	U8610964	9102894	U8800041
Straight	Absolute Bridge	3 in. (76.2 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-30	U8623035	9122244	U8800091
Straight	Absolute Bridge	3 in. (76.2 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-30-1-6M	U8623036	9122244	U8800091
Straight	Absolute Bridge	3 in. (76.2 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-30-200K-1M	U8610528	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-40	U8623038	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-40-1-6M	U8623039	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-40-200K-1M	U8610675	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-45-200K-1M	U8623043	9122244	U8800091
Straight	Absolute Bridge	5 in. (127 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-50	U8623058	9122244	U8800091
Straight	Absolute Bridge	5 in. (127 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-50-1-6M	U8623313	9122244	U8800091
Straight	Absolute Bridge	5 in. (127 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-50-200K-1M	U8623314	9122244	U8800091
Straight	Absolute Bridge	6 in. (152.4 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-60	U8623059	9122244	U8800091
Straight	Absolute Bridge	6 in. (152.4 mm)	1 MHz to 6 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-60-1-6M	U8623060	9122244	U8800091
Straight	Absolute Bridge	6 in. (152.4 mm)	200 kHz to 1 MHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-60-200K-1M	U8610537	9122244	U8800091
Straight	Absolute Bridge	7 in. (177.8 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-70	U8614292	9122244	U8800091
Straight	Absolute Bridge	8 in. (203.2 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-80	U8623062	9122244	U8800091
Straight	Absolute Bridge	9 in. (228.6 mm)	50 kHz to 500 kHz	0.125 in. (3.17 mm)	Triax Fischer	MTF-90	U8623233	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Microdot	MXP305-40	U8610548	9102894	U8800041
Straight	Absolute Bridge	6 in. (152.4 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Microdot	MXP-60	U8616160	9102894	U8800041
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF-40	U8623131	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	200 kHz to 1 MHz	0.05 in. (1.27 mm)	Triax Fischer	MXTF-40-200K-1M	U8616155	9122244	U8800091
Straight	Absolute Bridge	10 in. (254 mm)	1 MHz to 3 MHz	0.094 in. (2.39 mm)	Microdot	MYP-100-1-3M	U8610818	9102894	U8800041
Straight	Absolute Bridge	5 in. (127 mm)	200 kHz to 1 MHz	0.094 in. (2.39 mm)	Microdot	MYP-50-200K-1M	U8610769	9102894	U8800041
Straight	Absolute Bridge	4 in. (101.6 mm)	50 kHz to 500 kHz	0.094 in. (2.39 mm)	Triax Fischer	MYTF-40	U8623137	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	1 MHz to 3 MHz	0.094 in. (2.39 mm)	Triax Fischer	MYTF-40-1-3M	U8629739	9122244	U8800091
Straight	Absolute Bridge	4 in. (101.6 mm)	200 kHz to 1 MHz	0.094 in. (2.39 mm)	Triax Fischer	MYTF-40-200K-1M	U8616156	9122244	U8800091
Straight	Absolute Bridge	6 in. (152.4 mm)	50 kHz to 500 kHz	0.094 in. (2.39 mm)	Triax Fischer	MYTF-60	U8616161	9122244	U8800091
Straight	Absolute Bridge	5 in. (127 mm)	200 kHz to 1 MHz	0.062 in. (1.57 mm)	Triax Fischer	MZTF-50-200K-1M	U8616137	9122244	U8800091
Straight	Absolute Bridge	6 in. (152.4 mm)	50 kHz to 500 kHz	0.062 in. (1.57 mm)	Triax Fischer	MZTF-60	U8610915	9122244	U8800091