



Vanta™ Handheld XRF Analyzer

Rugged. Revolutionary. Productive.

EVIDENT

The Right Answer in Any Environment



The Olympus Vanta™ handheld XRF provides immediate, on-site elemental measurements for a range of geochemical applications. Vanta analyzers provide power and flexibility across the entire mineral resource cycle:

- › Greenfield and brownfield exploration
- › Ore grade and process control
- › Environmental monitoring and remediation
- › Academic/educational research and teaching within the geological/environmental sciences

Vanta handheld XRF analyzers are IP55* rated to withstand rain, dirt, and dust and are drop tested to department of defense standards (MIL-STD-810G) to help prevent breakages and costly repairs. Their rugged and durable design makes Vanta devices resistant to damage for greater uptime and a lower cost of ownership.

With our innovative Axon Technology™, you get the right answer no matter the environment or working conditions. Vanta analyzers for geochemistry feature software designed in cooperation with industry experts to help meet the needs of mineral resource, environmental companies, and educational institutions. Integrated GPS enables users to instantly geo-reference exploration and environmental samples. Connectivity via wireless LAN and Bluetooth® gives users the flexibility to send results to base in real-time and seamlessly integrate data into third-party geological software programs. Vanta analyzers also offer onboard spectra viewing to quickly discriminate spectral overlaps.



Vanta™ XRF analyzers are effectively used across a range of mineral deposit types including:

- › Base metals such as Cu, Pb, Zn, Ag, and Mo
- › Gold, including pathfinders, and litho-geochemistry
- › Uranium +/- rare earth elements and pathfinders
- › Nickel sulfide and laterite deposits
- › Iron ore and bauxites
- › Rare earth elements (REEs) such as La, Ce, Pr, and Nd
- › REE pathfinders including Y, Th, and Nb
- › Phosphates, potash, limestone, magnesite, and other industrial minerals
- › Epithermal Sn, W, Mo, Bi, and Sb deposits
- › Mineral sands such as Ti and Zr
- › Coal, oil, and gas through mud logging and trace element chemistry

Mineral Exploration



Vanta™ analyzers offer rapid return on investment (ROI) by providing users with “decision quality” geochemical data much faster than traditional laboratory techniques. Rapid, accurate decision-making at the exploration stage enables field time to be used more effectively, maximizes exploration (drilling and analytical) budgets, and advances project timeframes.

The easy-to-use interface can be customized with settings useful for specific sites, users, projects, and applications. Geologists can store multiple sample and matrix-specific calibration models for optimal performance depending on the minerals of interest at the specific site.

The durable design and advanced Axon Technology™ found in every Vanta analyzer enables geologists to work in remote areas with confidence that the device is built to withstand harsh environments and that answers provided are reliable and repeatable.

In mineral exploration applications, Vanta analyzers are effective for:

- › Due diligence during property acquisition
- › Analyzing the qualitative chemistry of rock, chip, soil, and sediment samples at the early regional reconnaissance and mapping stages
- › Gathering quantitative data during first-pass regional soil, sediment, till, and trenching stages
- › Identifying mineralized trends and anomalies, defining drill targets, and extending soil sample lines
- › Adapting sampling and mapping programs in real-time to maximize exploration budgets
- › Pre-screening samples to maximize the efficiency of off-site laboratory testing
- › Increasing sample density in the most prospective areas
- › Analyzing air core, RAB, RC, and diamond core samples during the drilling phase as the samples come out of the ground

Ore Grade and Process Control



Vanta™ analyzers help mining companies maintain their profitability in many open-pit and underground mines and in their associated processing facilities. On-site labs generally take hours or days to provide results. With the Vanta handheld XRF, you can get the right answer well in advance of a laboratory result. In some mine-site situations, this can mean huge cost savings. Vanta analyzers enable mine geologists to engage in intelligent and accurate grade control and metallurgists to monitor the efficiency and fine-tune the beneficiation process in real time.

Vanta analyzers are pre-calibrated using a wide range of industry standard certified reference materials (CRMs) providing users with excellent out of the box accuracy. Simple, intuitive software features enable users to fine tune this factory calibration, where necessary, for optimal performance on different geological samples and matrices.

In ore grade and process control, Vanta handheld XRF analyzers provide measurable ROI through:

- Reduced reliance on mine-site labs by instant screening of open-pit blast hole samples
- Improved underground grade control when combined with appropriate sampling methodologies
- Analysis of stockpile material to aid blending and feeding of the mill
- Real-time analysis of feeds, precipitates, concentrates, and tailings for immediate adjustments in the processing plant
- Analysis of penalty elements in concentrates and Au bars
- Analysis of S and other elements to determine flux adjustments in samples
- Analysis of Si as a proxy for quartz to inform ball mill grind times and optimize recoveries
- Analysis of raffinates and various lean and rich liquid mixes in SX/EW operations
- Testing of liquid waste streams as part of hydromet processes, particularly in copper and precious metals plants



Environmental Monitoring and Remediation

Vanta™ handheld XRF analyzers are used to identify elements of interest in soil, sediment, dust, and tailings as part of typical environmental monitoring remediation processes in and around active and closed industrial properties. Some active operations are using handheld XRF analyzers to monitor SiO_2 dust on processing equipment, Pb use in fire assay labs, and control Hg and As vapors in production environments in Au refineries. To help customers meet regulatory requirements, Vanta analyzers act as a fast and reliable screening tool that provide quantitative records of environmental monitoring that are easily archived.

Academic Research and Education

Portable XRF equipment, like Vanta analyzers, are playing an increasing role in academic studies relating to geological and environmental research projects and as a teaching tool. Vanta analyzers can aid in-house university laboratory methods, support undergraduate and post-graduate research projects, and facilitate teaching methods during routine coursework. The rapid results provided by Vanta handheld XRF analyzers can help educate students in modern analytical methods, aid in the identification of all types of samples, and provide a deeper understanding of mineral deposition and ore genesis relating to mineral deposit studies.

Durable and Reliable for Any Job in Any Environment

Rugged

Mines and outdoor environments can be tough on electronic devices, often causing breakdowns that cost time and money. Vanta analyzers are durable for increased uptime and a low cost of ownership.

Vanta™ devices are drop tested and IP55 rated* dust and immersion resistant to protect against the hazards found in even the most challenging environments. They can withstand a temperature range of -10 °C to 50 °C (14 °F to 122 °F), so you achieve 100% uptime without waiting for your analyzer to cool, even in hot environments.** The detector shutter on silicon drift detector models helps prevent punctures so you can analyze rough surfaces with confidence.

Revolutionary

Every circuit, contour, and interface of Vanta handhelds is engineered to be the best of its kind. Vanta analyzers incorporate Olympus' Axon Technology™, a breakthrough in XRF signal processing that delivers accurate and repeatable test results. Axon Technology uses ultra-low-noise electronics enabling higher X-ray counts per second and faster results. Coupled with a quad-core processor, Axon Technology makes Vanta analyzers remarkably responsive, pushing the limits of performance so you get the best results in the least amount of time. Axon Technology provides both test-to-test and instrument-to-instrument repeatability. Whether it's your first test on your first analyzer or your thousandth test with your hundredth analyzer, Vanta handheld XRF gives you the same result every time.

Productive

Vanta analyzers maximize user throughput and make data archiving easy. Application-specific software features improve user productivity for fast return on investment.

- › A new, intuitive interface enables the user to quickly navigate the device's settings and software functions
- › The UI can be configured based on a customer's specific needs; users can customize what software features and functions are displayed on the main screen
- › Data are easily exported via a USB flash drive, wireless LAN, or Bluetooth®
- › Vanta analyzers feature a clear, bright LCD touch screen that is readable in any light
- › Ergonomic buttons and an industrial-grade, push-button joystick enable users to easily navigate the system with gloved hands

Olympus' Vanta handheld XRF analyzer offers embedded GPS so users can pair results with precise GPS coordinates to document and map the location of elements. The optional 5-megapixel panoramic camera combines images of XRF data with GPS coordinates for inclusive archiving and streamlined reporting, which provides unmatched data traceability to the field.

Vanta Analyzers for Mining

The VMR and VCR models are the Vanta™ analyzers typically used for mineral exploration. No matter the model, the rugged, fast, reliable Vanta analyzer features Olympus' Axon Technology™, and is rated to pass a 4-foot drop test. C and L Series analyzers are IP55 rated, and Element and M Series analyzers are IP54 rated.



M Series

Our most powerful Vanta analyzers feature exceptional performance. Each M Series analyzer comes equipped with a large-area silicon drift detector, your choice of either a rhodium (Rh) or tungsten (W) anode, and a 50 kV X-ray tube.

C Series

The C Series combine value with superior speed, limits of detection (LODs), and elemental range. Each C Series analyzer is equipped with a silicon drift detector and your choice of a 40 kV X-ray tube with a rhodium (Rh) or tungsten (W) anode, or a 50 kV X-ray tube with a silver anode.

L Series

Get the ruggedness, ease of use, and data management features of Vanta analyzers in a cost-effective PIN instrument. The L Series is designed for maximum uptime and a lower cost of ownership for reliability in the field.



Vanta Element

Featuring advanced Axon Technology™ processing, the rugged Vanta Element handheld analyzer is an affordable solution. Leverage its connectivity options to streamline your process.

Olympus

Olympus is a leader in XRF technology with a reputation for quality and accuracy. The Olympus International Mining Group (IMG) is an internal group of natural resource specialists wholly focused on geochemical applications of XRF and XRD. The IMG has unparalleled expertise in utilizing portable XRF technology for a range of in-field geological scenarios. Olympus' global network of support staff provide a level of ongoing service to the customer that includes support for testing methods, specific calibrations, and user training.



Evident Scientific, Inc.
48 Woerd Avenue
Waltham, MA 02453, USA
Tél. : (1) 781-419-3900

