


See the Big Picture and Save Time Use a B-Scan Buggy



38DL PLUS[®] Thickness Gage with Encoded B-Scan Software Option and Buggy



B-scan review in the GageView Thickness program

Advantages

- Connect an encoder to the 38DLP to produce single-line encoded thickness B-scans
- Capture and display a thickness profile over a linear distance
- Save B-scans to review on the 38DLP or upload to the GageView[®] Thickness interface for expanded reporting capabilities

Applications

Gain valuable insight through analysis of corroded or pitted areas of:

- Piping
- Tank floors and walls