


Sensor Solutions for Automated Inspection Systems



As an industry-leading NDT systems manufacturer, Olympus provides high-quality sensor solutions for a variety of applications.

Our industry-leading turnkey inspection systems are complemented by our wide range of sensor solutions, including phased array UT and conventional UT sensors. In addition, we offer a wide range of sensors for aging ultrasonic inspection systems.

Olympus sensor solutions support:

- Bar, tube, and pipe systems
- Rotating head systems
- ROWA systems
- Plate inspection systems
- Rail and wheel systems
- Composite inspection systems
- Velocity inspection systems



Key Advantages of Olympus Sensor Solutions

1. Fast turnarounds mean shorter lead times

Olympus can deliver on your custom sensor requests quickly to minimize downtime and maximize production.

2. Large inventory available


Through our expanded State College manufacturing facility, we have streamlined the build process on various transducer models to offer more off-the-shelf solutions.

3. Increased wear properties for custom solutions

We now offer additive conformal coating processes that increase the lifespan of immersion transducers for cost savings and minimized downtime.

4. Competitive pricing

Manage your budgets and see significant cost savings by taking advantage of our competitive pricing.



To learn more, contact our Systems and Integration team at www.olympus-ims.com.

www.olympus-ims.com

OLYMPUS[®]

OLYMPUS CORPORATION OF THE AMERICAS

48 Woerd Avenue, Waltham, MA 02453, USA, Tel.: (1) 781-419-3900
110 Magellan Circle, Webster TX, 77598, USA, Tel.: (1) 281-922-9300

OLYMPUS SCIENTIFIC SOLUTIONS AMERICAS is certified to ISO 9001.
Olympus and the Olympus logo are trademarks of Olympus Corporation or its subsidiaries.