

U-AC2-7

Abbe Condenser



SPECIFICATIONS

Global item code / Local code for USA	N4257400 / 6-U1112	
Predecessor product information	None	
Product Category	Condenser	
Optical specification	Optical type	Abbe
	Contrast Method	BF
	Max. N.A.	1.1
	Working distance	0.7 mm (with immersion oil)
	Applicable objective powers	4X (Widefield: FN 22) 10X - 100X (Super widefield: FN 26.5)
	Frame	Dovetail
ESD function	N/A	
Weight	174 g	
Country of Origin	China	

SYSTEM ENVIRONMENT LIMITATIONS FOR OPERATION


Environment	Indoor use
Temperature T0 [°C]	5 - 40
Humidity RH0 [%]	Maximum 80% (up to 31°C) (no condensation) Usable humidity declines linearly as temperature rises above 31°C 34°C (70%) to 37°C (60%) to 40°C (50%)
Pollution level (IEC60664)	2
Over voltage category (IEC60664)	II

U-AC2-7

PACKING LIST

Item	Quantity
Condenser	1
Cover	1

MAIN DIMENSION



(Unit: mm)

· Specifications and appearances are subject to change without any notice or obligation on the part of the manufacturer.

EVIDENT CORPORATION

AM5427 01

Issued in January, 2023