

U-LH100L-3

100 W Halogen Lamp Housing



SPECIFICATIONS

Global item code / Local code for USA	N5727700 / 5-UL1237	
Predecessor product information	None	
Product Category	Light Source Unit	
Type	Light Source Units	
Light source	Halogen bulb	
Bulb centerable	Pre-centered	
Brightness	12 V, 100 W	
Cable length	800 mm	
Accepted Lamp	12V100WHAL (high-intensity lamp) 12V100WHAL-L (long-life lamp)	
Power supply method	Power supply unit	
Attached method	Frame / Illuminator	Fitting mount
	Halogen bulb	Lamp socket with bulb clamping lever
	Cable connection	Connector
ESD function	N/A	
Weight	880 g	
Country of Origin	Japan	

SYSTEM ENVIRONMENT LIMITATIONS FOR OPERATION


Environment	Indoor use
Temperature T0 [°C]	0 – 40
Humidity RH0 [%]	30 – 90

U-LH100L-3

PACKING LIST

Item	Quantity
Lamp Housing	1

MAIN DIMENSION



(Unit: mm)

· Specifications and appearances are subject to change without any notice or obligation on the part of the manufacturer.