

U-LH100IR

100 W Halogen Lamp Housing



SPECIFICATIONS

| | | |
|---------------------------------------|---|--------------------------------------|
| Global item code / Local code for USA | N2757600 / 5-UL1227I | |
| Predecessor product information | None | |
| Product Category | Light Source Units | |
| IR Observation | Available | |
| Light source | Halogen bulb | |
| Bulb centerable | Pre-centered | |
| Brightness | 12 V, 100 W | |
| Cable length | 290 mm | |
| Accepted Lamp | 12V100WHAL (high-intensity lamp) 12V100WHAL-L (long-life lamp) | |
| Power supply method | Power supply unit | |
| Attached method | Frame/Illuminator | Fitting mount |
| | Halogen bulb | Lamp socket with bulb clamping lever |
| | Thermal Reflection Filter(45SCF) | Fitting mount (ø45 mm) |
| | Cable connection | Connector |
| ESD function | N/A | |
| Weight | 880 g | |
| Country of Origin | Japan | |

SYSTEM ENVIRONMENT LIMITATIONS FOR OPERATION


| | |
|---------------------|------------|
| Environment | Indoor use |
| Temperature T0 [°C] | 0 – 40 |
| Humidity RH0 [%] | 30 – 90 |

U-LH100IR

PACKING LIST

| Item | Quantity |
|--------------|----------|
| Lamp Housing | 1 |

MAIN DIMENSION



(Unit: mm)

· Specifications and appearances are subject to change without any notice or obligation on the part of the manufacturer.