

BX3M-LEDT

LED Lamp Housing for BX3M Transmitted



SPECIFICATIONS

Global item code / Local code for USA	N5232900 / 5-UL410	
Predecessor product information	None	
Product Category	Light Source Unit	
Lamp house	Observation method	Transmitted (Bright field, Dark field, polarization, DIC)
	Light source	White LED (5700K)
	Maximum current	700 mA
	Cable length	165mm
	Power supply method	Controller for LED (ex:BX3M-PSLED)
Attached method	Frame	Fitting mount
	Cable connection	Connector
ESD function	N/A	
Weight	0.5 kg	
Country of Origin	China	

SYSTEM ENVIRONMENT LIMITATIONS FOR OPERATION


Environment	Indoor use
Temperature T0 [°C]	5 - 40
Humidity RH0 [%]	Maximum 80% (up to 31°) (no condensation) Usable humidity declines linearly as temperature rises above 31° 34° (70%) to 37° (60%) to 40° (50%)

BX3M-LEDT

PACKING LIST

Item	Quantity
LED Lamp Housing	1

MAIN DIMENSION



(Unit: mm)

· Specifications and appearances are subject to change without any notice or obligation on the part of the manufacturer.