

BX3M-ILH

Illuminator Holder for BXFM



SPECIFICATIONS

Global item code / Local code for USA	N5235500/5-UR727	
Predecessor product information	None	
Product category	Illuminator Holder	
Total weight limit of the units	Without the assist spring for BXFM (BXFM-ILHSPU)	Upper limit: 7.5 kg, lower limit: unlimited
	With the assist spring for BXFM (BXFM-ILHSPU)	Upper limit: 11.5 kg, lower limit: 6.5 kg * * If the total weight is lighter than 6.5 kg, accuracy of the fine focusing knob of the BXFM frame can not be assured.
Attached method	BXFM frame	Clamping screw
	Illuminator	Clamping screw
	Control box(U-CBS)	Clamping screw
ESD function	N/A	
Weight	Illuminator holder	1.2kg
	Bracket	0.1kg
Country of Origin	Japan	

SYSTEM ENVIRONMENT LIMITATIONS FOR OPERATION

Environment	Indoor use
Temperature T0 [°C]	5 - 40
Humidity RH0 [%]	Maximum 80% (up to 31°C) (no condensation) Usable humidity declines linearly as temperature rises above 31°C 34°C (70%) to 37°C (60%) to 40°C (50%)

RESTRICTIONS


Do not use BX3M-ILH in combination with U-ST stand because this makes the system unstable.

BX3M-ILH

PACKING LIST

Item	Quantity
Illuminator Holder	1
Bracket	1
Centering knob	2
Screw 4 X 35mm	4
Screw 4 X 8mm	2

MAIN DIMENSION



(Unit: mm)

· Specifications and appearances are subject to change without any notice or obligation on the part of the manufacturer.